

# PRODUCT INFORMATION PACKET

FASCO®

Model No: A166  
Catalog No: A166  
Rectangular Outlet Shaded Pole Centrifugal Blower, 115 Volts, Flange: Yes  
Centrifugal Blowers



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Voltage	115 V	Motor Type	Shaded Pole
Thermal Protection	Thermally	Speed	3160 rpm
Current	1.50/1.37 A	Number of Speeds	1
Frequency	50/60 Hz	Phase	1
Ambient Temperature	40 °C	UL	Yes
Insulation Class	B	CSA	Yes

**Technical Specifications**

Blower Outlet Shape	Rectangle	Motor Enclosure	Open
Blower Outlet Flange	Yes	Bearing Type	Sleeve

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021