

PRODUCT INFORMATION PACKET

FASCO®

Model No: A170

Catalog No: A170

Round Outlet Shaded Pole OEM Replacement Draft Inducer Blower, 115 Volts, Flange: No
Draft Inducer Blowers



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Voltage	115 V	Motor Type	Shaded Pole
Thermal Protection	Thermally	Speed	3400 rpm
Current	2.3 A	Number of Speeds	1
Frequency	60 Hz	Phase	1
Ambient Temperature	40 °C	UL	Yes
Insulation Class	B	CSA	Yes

Technical Specifications

Blower Outlet Shape	Round	Motor Enclosure	Open Fan Cooled
Blower Outlet Flange	No	Bearing Type	Ball

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021