

# PRODUCT INFORMATION PACKET

FASCO®

Model No: A197

Catalog No: A197

Round Outlet Three Phase OEM Replacement Draft Inducer Blower, 33-110 Volts, Flange: No  
Draft Inducer Blowers



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



### Nameplate Specifications

Voltage	<b>33-110 V</b>	Motor Type	<b>Three Phase</b>
Thermal Protection	<b>Thermally</b>	Speed	<b>1500-4700 rpm</b>
Current	<b>1 A</b>	Number of Speeds	<b>1</b>
Frequency	<b>60-180 Hz</b>	Phase	<b>3</b>
Ambient Temperature	<b>40 °C</b>	UL	<b>Yes</b>
Insulation Class	<b>B</b>	CSA	<b>Yes</b>

### Technical Specifications

Blower Outlet Shape	<b>Round</b>	Motor Enclosure	<b>Open</b>
Blower Outlet Flange	<b>No</b>	Bearing Type	<b>Ball</b>

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021