

# PRODUCT INFORMATION PACKET

FASCO®

Model No: A241

Catalog No: A241

Rectangular Outlet Shaded Pole OEM Replacement Draft Inducer Blower, 208-230 Volts, Flange: No  
Draft Inducer Blowers



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



### Nameplate Specifications

|                     |             |                  |               |
|---------------------|-------------|------------------|---------------|
| Voltage             | 208-230 V   | Motor Type       | Shaded Pole   |
| Thermal Protection  | Thermally   | Speed            | 2800/3200 rpm |
| Current             | 0.56/0.65 A | Number of Speeds | 1             |
| Frequency           | 50/60 Hz    | Phase            | 1             |
| Ambient Temperature | 40 °C       | UL               | Yes           |
| Insulation Class    | B           | CSA              | Yes           |

### Technical Specifications

|                      |           |                 |      |
|----------------------|-----------|-----------------|------|
| Blower Outlet Shape  | Rectangle | Motor Enclosure | Open |
| Blower Outlet Flange | No        | Bearing Type    | Ball |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021