

PRODUCT INFORMATION PACKET

FASCO®

Model No: B45267
Catalog No: B45267
Rectangular Outlet Shaded Pole Centrifugal Blower, 115 Volts, Flange: Yes
Centrifugal Blowers



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Voltage	115 V	Motor Type	Shaded Pole
Thermal Protection	Thermally	Speed	1600 rpm
Current	2.9 A	Number of Speeds	2
Frequency	60 Hz	Phase	1
Ambient Temperature	40 °C	UL	No
Insulation Class	B	CSA	Yes

Technical Specifications

Blower Outlet Shape	Rectangle	Motor Enclosure	Open
Blower Outlet Flange	Yes	Bearing Type	Sleeve

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021