

# PRODUCT INFORMATION PACKET



Model No: J591  
Catalog No: J591  
Rectangular Outlet Shaded Pole Centrifugal Blower, 120 Volts, Flange: No  
Transflow / Crossflow Blowers



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

Voltage	120 V	Motor Type	Shaded Pole
Thermal Protection	Impedence	Speed	3100 rpm
Current	1.1 A	Number of Speeds	1
Frequency	60 Hz	Phase	1
Ambient Temperature	40 °C	UL	Yes
Insulation Class	A	CSA	Yes

**Technical Specifications**

Blower Outlet Shape	Rectangle	Motor Enclosure	Open
Blower Outlet Flange	No	Bearing Type	Sleeve

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021